STEALTH-VAC™ VACUUM TWEEZER™ Kit

STEALTH-VAC™ ESD-SAFE Kit - Normally Open VACUUM PEN™ - Operates On Compressed Air Or Nitrogen

The STEALTH-VAC[™] operates directly on 30 to 70 psi FILTERED compressed air or nitrogen. The vacuum is normally ON. The compressedair-powered tools are our most powerful VACUUM TWEEZER™ tools. The vacuum level can be controlled by adjusting the input pressure. At 10 psi input the vacuum level is 2 InHg with 1 lpm of free air flow, at 30 psi input the vacuum level is 10 InHg with 3 lpm of free air flow and at 70 psi input the vacuum level is 20 InHg with 4 lpm of free air flow. Includes five bent probes mounted with Non-marking Static Dissipative Buna-N Cup sizes 3/32" (2.38mm), 1/8" (3.18mm), 3/16" (4.76mm), 1/4" (6.35mm), and 3/8" (9.53mm), as well as four straight probes mounted with Non-marking Static Dissipative Buna-N Cup sizes 1/8" (3.18mm), 1/4" (6.35mm), 3/8" (9.53mm) and 1/2" (12.70mm).

The normally opened STEALTH-VAC™ Kit includes:

- STEALTH-VAC[™] NORMALLY OPEN VACUUM PEN[™]
- COILED-VACUUM-HOSE-6 (VCH-1/16-6)
- SET OF NINE VACUUM TIPS (VCS-9-B)
- 1/8" NPT TO 1/16" BARB THREADED ADAPTER FOR SUPPLY LINE (V3014-1/8NPT)

STEALTH-VAC[™] is ready for use as follows:

- 1. Attach a VACUUM TWEEZER™ tip slightly smaller than the 技术咨询与报价 part you need to handle.
- 2. Merely touch the vacuum tip squarely to the part. The part is now grasped.
- 3. Move the part to where you want it. Tap the control button to release the part.

VVSV-NO (normally open)

VVSV-NO-KIT (with Pen Holder VBM-3)



STEALTH-VAC™ ELITE VACUUM TWEEZER™ Kit

STEALTH-VAC™ ELITE ESD-SAFE Kit - Normally Closed VACUUM PEN™ - Operates On Compressed Air Or Nitrogen

The STEALTH-VACTM ELITE operates directly on 30 to 50 psi FILTERED compressed air or nitrogen. The normally closed STEALTH-VACTM Elite VACUUM PEN™ contains a whisper quiet venturi vacuum generator that is activated only when the control button is depressed. This helps conserve factory compressed air when the tool is not in use. The vacuum level can be controlled by adjusting the input pressure. At 10 psi input the vacuum level is 2 InHg with 1 lpm of free air flow, at 30 psi input the vacuum level is 10 InHg with 3 lpm of free air flow and at 70 psi input the vacuum level is 20 InHg with 4 Ipm of free air flow. Includes five bent probes mounted with Non-marking Static Dissipative Buna-N Cup sizes 3/32" (2.38mm), 1/8" (3.18mm), 3/16" (4.76mm), 1/4" (6.35mm), and 3/8" (9.53mm), as well as four straight probes mounted with Non-marking Static Dissipative Buna-N Cup sizes 1/8" (3.18mm), 1/4" (6.35mm), 3/8" (9.53mm) and 1/2" (12.70mm).

The normally closed STEALTH-VAC™ ELITE Kit includes:

- STEALTH-VAC[™] ELITE NORMALLY CLOSED VACUUM PEN[™]
- COILED-VACUUM-HOSE-6 (VCH-1/16-6)
- SET OF NINE VACUUM TIPS (VCS-9-B).
- 1/8" NPT TO 1/16" BARB THREADED ADAPTER FOR SUPPLY LINE (V3014-1/8NPT)

STEALTH-VAC[™] ELITE is ready for use as follows:

- 1. Attach a VACUUM TWEEZER™ tip slightly smaller than the part you need to handle.
- 2. Touch the vacuum tip squarely to the part and depress and hold the button. The part is now grasped.
- 3. Move the part to where you want it. Release the control button to release the part.

VVSV-NC (normally closed)

VVSV-NC-KIT (with Pen Holder VBM-3)



Barbed hose filter – Inlet connection 1/16" (1.59mm) – Outlet connection 1/16" (1.59mm) ID hose. Recommended option to filter compressed air supply. These filters come with a replaceable 40 micron mesh o-ring filter. NOTE: See page 1 for replacement filter VF-40M-5.





Assembled

Unscrew to change filter

/irtual真空吸笔http://www.testeb.com/gongju/virtual/zhenkongxibi.html 深圳市格信达科技 18823303057、QQ:2104028976